

Dispensette® S


Innovative ideas with trusted technology – the new bottle-top dispenser Dispensette® S.

- New discharge tube with or without recirculation valve
- New valve system, no sealing rings necessary
- Faster priming due to improved flow technology
- Less force needed during dispensing especially for instruments with large volumes
- Volume selection with interior scalloped track for analog devices, enhances setting reproducibility
- New 1 ml size digital and analog

A Closer Look...

The bottle-top dispenser Dispensette® S has all the features that make dispensing safer and convenient.

Innovative ideas – trusted technology.



Easy Calibration Technique

Calibration and adjustments according to ISO 9001 and GLP are done within seconds.

NEW!

Discharge valve with safety ball

closes when discharge tube is not mounted

NEW!

Discharge tube

without recirculation valve

NEW!

Large viewport

NEW!

Hinged screw cap

doesn't get in the way when dispensing

Calibration mechanism

NEW!

Volume selection

using interior scalloped track

NEW!

Discharge tube

with recirculation valve

360° rotating

valve block

with GL 45 thread

NEW!

Filling valve olive-shaped

for firmer attachment of the filling tube

Recirculation tube

for discharge tubes with recirculation valve

Telescoping

filling tube